

SPECIFICATIONS

FR055WA03/04 2" neodymium, alu-cone fullranges, 4/8 ohm

The 2" fullrange transducers FR055WA03 (4 ohm) and FR055WA04 (8 ohm) were designed especially for high quality multimedia and lifestyle speakers, and for personal audio products, where sound reproduction without compromises is required. Will additionally work well as a midrange/treble transducer in small speaker products in combination with for instance a small subwoofer unit.

FEATURES

- True full-range design with on-axis output to beyond 20kHz
- Upgraded design with higher efficiency and improved high frequency output
- Copper cap on center pole to reduce voice coil inductance and to minimize variations in voice coil inductance as a function of voice coil position
- Dual neodymium magnet structure for high efficiency and almost ideal magnetically shielding
- Black anodized alu cone for better heat transfer
- Vented polymer chassis for lower air flow speed reducing audible distortion
- Vented voice coil former for reduced distortion and compression
- Heavy-duty black fiber glass voice coil bobbin to reduce mechanical losses resulting in better dynamic performance and low-level details
- Large motor with 22 mm voice coil diameter for better control and power handling
- Low-loss suspension (high Qm) for better reproduction of details and dynamics
- Black motor parts for better heat transfer to the surrounding air
- Conex spider for better durability under extreme conditions
- Gold plated terminals to ensure long-term trouble free connection



NOMINAL SPECIFICATIONS

Notes	Parameter	FR055WA03		FR055WA04		Unit
		Before burn-in	After burn-in	Before burn-in	After burn-in	
	Nominal size	2		2		[inch.]
	Nominal impedance	4		8		[ohm]
	Recommended max. upper frequency limit	full range		full range		[kHz]
1, 4	Sensitivity, 2.83V/1m	86.5		83		[dB]
2, 4	Power handling, short term, IEC 268-5, no additional filtering	40		40		[W]
2, 4	Power handling, long term, IEC 268-5, no additional filtering	20		20		[W]
2, 4	Power handling, continuous, IEC 268-5, no additional filtering	4		4		[W]
2, 4	Power handling, continuous, IEC 268-5, 135 Hz HP 12dB/oct.	10		10		[W]
	Effective radiating area, S _d	15.6		15.6		[cm ²]
3, 4, 6	Resonance frequency (free air, no baffle), F _s	142	128	145	131	[Hz]
	Moving mass, incl. air (free air, no baffle), M _{ms}	1.60		1.54		[g]
3, 4	Force factor, Bxl	2.7		3.3		[N/A]
3, 4, 6	Suspension compliance, C _{ms}	0.785	0.96	0.785	0.96	[mm/N]
3, 4, 6	Equivalent air volume, V _{as}	0.27	0.33	0.27	0.33	[lit.]
3, 4, 6	Mechanical resistance, R _{ms}	0.16	0.16	0.16	0.16	[Ns/m]
3, 4, 6	Mechanical Q, Q _{ms}	8.9	8.1	8.8	7.9	[-]
3, 4, 6	Electrical Q, Q _{es}	0.61	0.55	0.80	0.70	[-]
3, 4, 6	Total Q, Q _{ts}	0.57	0.51	0.73	0.66	[-]
4	Voice coil resistance, R _{DC}	3.1		6.2		[ohm]
5	Voice coil inductance, L _e (measured at 10 kHz)	0.062		0.10		[mH]
	Voice coil inside diameter	22		22		[mm]
	Voice coil winding height	4.7		4.7		[mm]
	Air gap height	2.0		2.0		[mm]
	Theoretical linear motor stroke, X _{max}	±1.35		±1.35		[mm]
	Magnet weight	27		27		[g]
	Total unit net weight excl. packaging	0.083		0.083		[kg]
3, 4, 5	K _{rm}					[mohm]
3, 4, 5	E _{rm}					[-]
3, 4, 5	K _{xm}					[mH]
3, 4, 5	E _{xm}					[-]

Note 1 Measured in infinite baffle.

Note 2 Tested in free air (no cabinet).

Note 3 Measured using a semi-constant current source, nominal level 2 mA.


Note 4 Measured at 25 deg. C

Note 5 It is generally a rough simplification to assume that loudspeaker transducer voice coils exhibit the characteristics of an inductor. Instead it is a far more accurate approach to use the more advanced model often referred to as the "Wright empirical model", also used in LEAP-4 as the TSL model (www.linearx.com), involving parameters K_{rm}, E_{rm}, K_{xm}, and E_{xm}. This more accurate transducer model is described in a technical paper [here at our web site](#).

Note 6 After-burn-in specifications are measured 12 hours after exiting the transducer by a continuous sine wave for 2 hours. The sine wave frequency equals the transducer F_s, at level 3.0/4.65 VRMS (4/8 ohm version). Units are not burned in before shipping.

SPECIFICATIONS

FR055WA03/04 2" neodymium, alu-cone fullranges, 4/8 ohm




Important!
Please observe that graphs on the left side of this page and the text files for download (below) are actual measurements of the drivers measured in infinite baffle and without any enclosure. Measuring the drivers in a finite baffle (like the baffle of most speaker cabinets) and in any size of enclosure will lead to different response curves.




[Download on-axis SPL response as .txt file](#)

Measuring conditions, SPL
Driver mounting: Flush in infinite baffle, back side open (no cabinet)
Microphone distance: 1.0 m
Input signal: 2.83 VRMS stepped sine wave
Smoothing: 1/6 oct.




[Download Impedance response as .txt file](#)

Measuring conditions, impedance
Driver mounting: Free air, no baffle, back side open (no cabinet)
Input signal: Stepped sine wave, semi-current-drive, nominal current 2 mA
Smoothing: None



[Download on-axis SPL response as .txt file](#)

Measuring conditions, SPL
Driver mounting: Flush in infinite baffle, back side open (no cabinet)
Microphone distance: 1.0 m
Input signal: 2.83 VRMS stepped sine wave
Smoothing: 1/6 oct.



[Download Impedance response as .txt file](#)


Measuring conditions, impedance
Driver mounting: Free air, no baffle, back side open (no cabinet)
Input signal: Stepped sine wave, semi-current-drive, nominal current 2 mA
Smoothing: None

SPECIFICATIONS



FR055WA03/04 2" neodymium, alu-cone fullranges, 4/8 ohm

HARMONIC DISTORTION



June 8, 2022


Measuring conditions, Harmonic Distortion

Driver mounting: In sealed, heavily stuffed enclosure, internal volume 0.5 lit.

Microphone distance: 0.5 m

Input signal: Stepped sine wave, 1.26 VRMS (FR055WA03) / 1.79 VRMS (FR055WA04)

Smoothing: 1/6 oct.




June 8, 2022

SPECIFICATIONS

FR055WA03/04 2" neodymium, alu-cone fullranges, 4/8 ohm

OUTLINE DRAWING (nominal dimensions)



CONNECTIONS



PACKAGING AND ORDERING INFORMATION

Part no. FR055WA03-01	4 ohm version, packed in pairs
Part no. FR055WA03-02	4 ohm version, packed in bulk (industrial) packaging
Part no. FR055WA04-01	8 ohm version, packed in pairs
Part no. FR055WA04-02	8 ohm version, packed in bulk (industrial) packaging

Latest update: June 12, 2022